

PREMIUM-PPE

CONTACT US

Support@Premium-PPE.com

www.Premium-PPE.com

888-267-1801




ASTM Level 2 & 3

Color	black
Filtration - BFE	>98%
Filtration - PFE	>98%
Fluid Resistance, mmHG	160
Delta P, mmH ₂ O/cm ²	<6.0
Flame Spread	Class 1
Ear loop	black elastic
Packaging	50/box - 500/cs



How to wear a mask correctly




Use elastic ear loops to place mask with the blue side as the outer layer.



Stretch mask to cover nose and mouth.



Pinch nose wire and mold to face.



Unhook elastic ear loops, discard, and wash hands.




8 50005 94239 9

Pieces: 50
GW (lbs): 0.45
Dimensions:
SKU: PPE-M-AS-1105B



20850005942331

Pieces: 40
Boxes: 8
GW (lbs): 4.28
Dimensions: 16x8x8
Per Pallet: 50
Per Layer: 10
Layers: 5



10850005942334

Pieces: 2,000
Boxes: 40
GW (lbs): 20.23
Dimensions: 21x16x16
Per Pallet: 24
Per Layer: 6
Layers: 4